

Level Plus[®]

Magnetostrictive Liquid Level Transmitters
with Temposonics[®] Technology

SoCLEAN[®] Data Sheet

- Sanitary and Electropolished Finish
- Inherent Accuracy ± 1 mm
- No Scheduled Maintenance or Recalibration
- Hazardous Area Certified



TEMPOSONICS® TECHNOLOGY

Temposonics® Technology is the manner in which MTS applies the principles of magnetostriction to create a reliable position measurement system for use in industrial environments. Inside the sensor a torsional strain pulse is induced in a specially designed magnetostrictive waveguide by the momentary interaction of two magnetic fields. One field comes from a moving magnet, which passes along the outside of the transducer tube, and the other field is generated from a current pulse which is applied to the waveguide. The interaction between these two magnetic fields produces a strain pulse which travels at sonic speed along the sensor waveguide, until the pulse is detected at the head of the transducer. The position of the moving magnet is precisely determined by measuring the elapsed time between the application of the current pulse and the arrival of the strain pulse. As a result, MTS is able to create a reliable position measurement system that is capable of providing an accurate and repeatable measurement.




Fig. 1: Time-based magnetostrictive position sensing principle

SoClean®

The Level Plus® SoClean® liquid level transmitter satisfies the demand for an accurate and robust liquid-level sensor with unsurpassed flexibility to meet most process application conditions. The SoClean® transmitter provides 3-in-1 measurement using one process opening for product level, interface level, and temperature measurements. Once the transmitter is installed and calibrated there is no requirement for scheduled maintenance or recalibration. **Set it and forget it!**

Features:

- 3-in-1 Measurement
 - Product
 - Interface
 - Temperature
- No Scheduled Maintenance or Recalibration
- Inherent Accuracy ± 1 mm
- Intrinsically Safe
- Sanitary Finish Ra 25 μ m (0.64 μ m)
- Electropolished Finish Ra 15 μ m (0.38 μ m)

Applications:

- Process Control
- Batching
- Bioreactor

Markets:

- Food and Beverage
- Pharmaceutical
- Cosmetics

Standard	Rating
FM 3610	Class I, Div. 1, Groups A, B, C, and D T4 Class I, Zone 0/1, AEx ia IIC T4 Ta= -50 to 71°C: IP65
C22.2 No. 157	Class I, Div. 1, Groups A, B, C, and D T4 Class I, Zone 0/1, Ex ia IIC T4 Ta= -50 to 71°C: IP65
EN 60079-11:2012	FM14ATEX0068X II ½ G Ex ia IIC T4 Ta= -50 to 71°C: IP65
IEC 60079-11:2011	IECEX FMG 14.0032 II ½ G Ex ia IIC T4 Ga/Gb Ta= -50 to 71°C: IP65

TECHNICAL DATA

Level Output	
Measured variable	Product level and interface level
Output signal /Protocol	Modbus RTU, DDA
Order length	Sanitary Pipe: 305 mm (12 in.) to 7620 mm (300 in.) Δ \S
Inherent Accuracy	±1 mm (0.039 in.)
Repeatability	0.001% F.S. or 0.381 mm (0.015 in.) * (any direction)
Temperature Output	
Measured variable	Average and multipoint temperatures
Temperature accuracy	±0.2 °C (0.4 °F) range -40 °C (-40 °F) to -20 °C (-4 °F)*, ±0.1 °C (0.2 °F) range -20 °C (-4 °F) to 70 °C (158 °F)*, ±0.15 °C (0.3 °F) range 70 °C (158 °F) to 100 °C (212 °F)*, ±0.5 °C (0.9 °F) range 100 °C (212 °F) to 105 °C (221 °F)
Electronics	
Input voltage	10.5 to 28 Vdc
Fail safe	High, Full scale for digital
Reverse polarity protection	Series diode
EMC	Stage 1: Line-to-ground surge suppression; IEC 61000-4-5, IEC 61326-3-2 Stage 2: Line-to-line and line-to-ground transient suppressors; IEC 61000-4-4, IEC 61326-3-2
Environmental	
Enclosure rating	NEMA Type 4X, IP65
Humidity	0 to 100% relative humidity, non-condensing
Operating temperatures	Electronics: -40 °C (-40 °F) to 71 °C (160 °F) Sensing element: -40 °C (-40 °F) to 125 °C (257 °F) \diamond Temperature element: -40 °C (-40 °F) to 105 °C (221 °F)
Vessel pressure	Rigid pipe: 2000 psi (138 bar)
Materials	Wetted parts: 316L stainless steel \dagger Non-wetted parts: 316L stainless steel, Epoxy coated aluminum
Field Installation	
Housing dimensions	Single cavity: 145 mm (5.7 in.) W x by 127 mm (5 in.) D x 109 mm (4.3 in.) H Dual cavity: 117 mm (4.6 in.) W x by 127 mm (5 in.) D x 206 mm (8.1 in.) H Stainless steel single cavity: 178 mm (7.1 in.) W x by 135 mm (5.3 in.) D x 153 mm (6 in.) H NEMA Type 4X: 87 mm (3.4 in.) W x by 124 mm (4.9 in.) D x 132 mm (5.2 in.) H
Mounting	
Rigid pipe	Tri-Clamp, ¾ in. Adjustable MNPT or BSPP fitting
Wiring	
Connections	4-wire shielded cable or twisted pair, Daniel Woodhead 6-pin male connector, 4570 mm (180 in.) integral cable with pigtail
Electrical Connections	
Single and Dual Cavity	¾ in. FNPT conduit opening, M20 for ATEX/IECEX version
NEMA Type 4X	½ in. FNPT conduit opening
Display	
Measured variables	Product level, interface level and temperature

* Whichever is greater



Δ Contact factory for longer lengths.

\diamond Contact factory for specific temperature ranges.

\dagger Contact factory for alternative materials.

\S Order length equals the measurement range plus the inactive zone.

TECHNICAL DRAWING



♦ End plug style comes with permanently mounted floats. These floats cannot be removed from the pipe.

ORDER CODE

1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22
L	P	S																			
a			b	c	d	e	f	g	h	i	j	k	l	m	n	o				p	

a	Sensor model
L P S	SoClean® Level Transmitter

b	Output
M	Modbus
D	DDA

c	Housing type
A	NEMA housing w/cable
B	NEMA housing w/terminal
C	NEMA housing w/connector
D	Single cavity with display
E	Dual cavity with display
L	SS single cavity w/display

d	Electronics mounting
1	Standard

e	Sensor pipe
C	Sanitary T-bar, TB
D	Sanitary drain-in-place DP
E	Sanitary clean-in-place CP
F	Sanitary drain-in-place no hole, DN

f	Materials of construction (Wetted parts)
1	316L stainless steel
2	Electropolished 316L stainless steel

Note: Contact factory for other materials

g	Process connection type
1	NPT adjustable
2	BSPP adjustable
4	Sanitary Tri-Clamp, Welded
5	Sanitary Tri-Clamp, Adjustable

h	Process connection size
B	1 in. (DN25)
D	2 in. (DN50)
E	2 ½ in. (DN65)
F	3 in. (DN80)
G	4 in. (DN100)
J	6 in. (DN150)
X	None

i	Number of DT's (Digital Thermometer)
0	None
1	One DT
5	5 DTs
K	Twelve DTs
M	Sixteen DTs

j	DT Placement
F	Evenly spaced per API
C	Custom
X	None

k	Notified body
C	CEC (FMC)
E	ATEX
F	NEC (FM)
I	IEC
X	None

l	Protection method
I	IS
X	No approval

(Continued on next page)

ORDER CODE

1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22
L	P	S																			
a			b	c	d	e	f	g	h	i	j	k	l	m	n	o					p

m	Gas group
A	Group A
B	Group B
C	Group C
D	Group D
1	IIA
2	IIB
3	IIC
X	None

n	Unit of measure
M	Metric - Millimeters
U	US customary - Inches

o	Length (no decimal spaces)				
X	X	X	X	X	Rigid Pipe: 12 to 300 in (code as 01200 to 30000)
X	X	X	X	X	Rigid Pipe: 305 to 7620 mm (code as 00305 to 07620)

p	Special
S	Standard Product

ORDERING NOTE





Accessories such as floats, cables, and displays have to be ordered separately. All accessories are shown in the Accessories Catalog (551103).


FREQUENTLY ORDERED ACCESSORIES – Additional options available in our [Accessories Catalog](#)  [551103](#)

General Notes:

1. Be sure that the float specific gravity is at least 0.05 less than that of the measured liquid as a safety margin at ambient temperature.
2. For interface measurement: A minimum of 0.05 specific gravity differential is required between the upper and lower liquids.
3. When the magnet is not shown, the magnet is positioned at the center line of float.
4. Drawings contained in this document are for reference only. Contact the factory for engineering drawings.

Sanitary floats	Pressure	Temp.	Magnet offset	Specific gravity	Material	Part number
	10.3 bar (150 psi)	149 °C (300 °F)	Yes	0.66	SS 200 Grit/ Ra 25 µm (0.625 µm)	401513 -2
					SS 240 Grit/ Ra 15 µm (0.375 µm)	401513 -4

Sanitary floats	Pressure	Temp.	Magnet offset	Specific gravity	Material	Part number
	22.4 bar (325 psi)	149 °C (300 °F)	Yes	0.63	SS 200 Grit/ Ra 25 µm (0.625 µm)	200931 -6
					SS 240 Grit/ Ra 15 µm (0.375 µm)	200931 -8

Low Lift off floats	Pressure	Temp.	Magnet offset	Specific gravity	Material	Part number
	8.6 bar (125 psi)	149 °C (300 °F)	Yes	0.48	SS 240 Grit/ Ra 15 µm (0.375 µm)	252228 -2

Document Part Number:

551694 Revision A (EN) 07/2015

LOCATIONS

USA

**MTS Systems Corporation
Sensors Division**
3001 Sheldon Drive
Cary, N.C. 27513, USA
Tel. +1 919 677-0100
Fax +1 919 677-0200
info.us@mtssensors.com
www.mtssensors.com

JAPAN

MTS Sensors Technology Corp.
737 Aihara-machi,
Machida-shi,
Tokyo 194-0211, Japan
Tel. +81 42 775-3838
Fax +81 42 775-5512
info.jp@mtssensors.com
www.mtssensors.com

FRANCE

MTS Systems SAS
Zone EUROPARC Bâtiment EXA 16
16/18, rue Eugène Dupuis
94046 Creteil, France
Tel. +33 1 58 4390-28
Fax +33 1 58 4390-03
info.fr@mtssensors.com
www.mtssensors.com

GERMANY

**MTS Sensor Technologie
GmbH & Co. KG**
Auf dem Schüffel 9
58513 Lüdenscheid, Germany
Tel. +49 2351 9587-0
Fax +49 2351 56491
info.de@mtssensors.com
www.mtssensors.com

CHINA

MTS Sensors
Room 504, Huajing Commercial Center,
No. 188, North Qinzhou Road
200233 Shanghai, China
Tel. +86 21 6485 5800
Fax +86 21 6495 6329
info.cn@mtssensors.com
www.mtssensors.com

ITALY

**MTS Systems Srl.
Sensor Division**
Via Diaz,4
25050 Provaglio d'Iseo (BS), Italy
Tel. +39 030 988 3819
Fax +39 030 982 3359
info.it@mtssensors.com
www.mtssensors.com

LEGAL NOTICES

MTS, Temposonics and Level Plus are registered trademarks of MTS Systems Corporation in the United States; MTS SENSORS and the MTS SENSORS logo are trademarks of MTS Systems Corporation within the United States. These trademarks may be protected in other countries. All other trademarks are the property of their respective owners.

Copyright © 2015 MTS Systems Corporation. No license of any intellectual property rights is granted. MTS reserves the right to change the information within this document, change product designs, or withdraw products from availability for purchase without notice. Typographic and graphics errors or omissions are unintentional and subject to correction. Visit www.mtssensors.com for the latest product information. Product change notification alerts are available through the MTS Product Change Management System; register at www.mtssensors.com/PCMS.

